



VT-259D 9W A60 PLASTIC BULB SAMSUNG CHIP 3000K B22 DIMMABLE



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 60 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for B22 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Dimmable:	Yes
CRI:	>80
Body Type:	Thermoplastic
Color Temperature:	3000K
Model:	VT-259D-N
Watts:	8.5
Lumens:	806
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	60
Unit Color:	White
Color for Web:	Warm White
Dimension:	60x108mm
Operation Temperature:	-20°C to +45°C
Instant Start:	0-100% in < 1s
On/Off Cycles:	>20000
Base:	B22
Shape:	A60
Beam Angle:	200°
LED Chip Type:	SMD-Samsung Chip
Long Life:	20,000 Hours
IP Rating:	IP20
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
Samsung:	Yes



IP20
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	21852
Model:	VT-259D-N
EAN:	3800157691079
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	0.06
Unit CBM:	0.000644
Dimension:	60x108mm

MASTER BOX PACKAGING

Box Qty:	96
Qty Per Pallet:	
Length (Box) mm:	60
Width (Box) mm:	60
Height (Box) mm:	112