


Pin Assignment:



				Rev.	ECN NO.	Description			Date	Name	
					TOLERANCE INCHES M/M						
5	USB4 SHELL~PC+ABS~BLACK			2	PCS	.X	.015	.30			
4	TPE~BLACK			10	G	.XX	.010	.10	Title: 1m USB4 40Gbps EPR(240W) Cable,twisted pair Black ABS hood		
3	USB4~CONNECTOR~WITH IC~NI PLATED			1	PCS	.XXX	.005	.05			
2	USB4~CONNECTOR~WITHOUT IC~NI PLATED			1	PCS	DRAWN BY		CUSTOMER :			
1	30AWG*4P+34AWG*1P+34AWG*4C+24AWG*1C+EAS(95%TC)~OD:5.1MM~BLACK~TPE			1.0	m	CHECK BY		CUSTOMER P/N :			
NO.	DESCRIPTION			Q' TY	UNIT	APPD BY		SCALE	NONE	DRAWING NO.:	Rev. A0
								UNIT	MM		
								DATE	2023.11.15	PSG92071	1/1