



Pin Assignment

PCB-P1		PCB-P2
RXp1+ B11		A2 TXp1+
RXn1- B10		A3 TXn1-
TXp1+ A2		B11RXp1+
TXn1- A3		B10RXn1-
RXn2- A10		B3 TXn2-
RXp2+ A11		B2 TXp2+
TXn2- B3		A10RXn2-
TXp2+ B2		A11RXp2+
CC A5		A5 CC
E-MARK		
VCONN B5		B5 VCONN
SBU2 B8		A8 SBU1
SBU1 A8		B8 SBU2
WAKE A13		A13WAKE
D- A7		A7 D-
D+ A6		A6 D+
VBUS (A4,A9,B4,B9)		A4,A9,B4,B9
10nF		10nF
GND(A1,A12,B1,B12)		A1,A12,B1,B12
Shell		Shell

				Rev.	ECN NO.	Description		Date	Name
					TOLERANCE		Title: 3m USB4 40Gbps EPR(240W) Active Cable,coaxial Black ABS hood		
					INCHES	M/M			
					.X	.015			
4	USB4 SHELL~AL~BLACK	2	PCS	.XX	.010	.10			
3	TPE~BLACK	10	G	.XXX	.005	.05			
2	USB4~CONNECTOR~WITH IC~NI PLATED~voltage adjuster	2	PCS	DRAWN BY		CUSTOMER :			
1	31AWG*8COX+31AWG*2COX+23AWG*2C+24AWG*1C+34AWG*1C+34AWG*4C +PSS(90%TC)~OD:5.3MM~BLACK~TPE	3.0	m	CHECK BY		SCALE	NONE	DRAWING NO.:	Rev. A0
				UNIT	MM				
				NO.	DESCRIPTION	Q' TY	UNIT	APPD BY	