



Trust Maxo 65W USB-C Charger - Black UK

Compact 65W USB-C Charger with included 2m USB-C cable

Article number: 25208

Barcode: 8713439252088

GTIN: 08713439252088

Core content

Brand	Trust
Product type	65W USB-C Charger
Colour	Black
Plug country code	UK
Key features	- 65W USB-C port to help you charge up quickly and easily* - Eco-friendly design made with 75% recycled materials - Charge any smartphone, tablet or laptop** with a USB-C connection - Sleek and compact design allows for high power output in a small form - Included 2m USB-C cable for convenient charging whenever, wherever - Safe charging: protects against overload, short-circuiting and overheating - Ideal travel charger: works with all wall power socket voltages worldwide (90-240V AC 60/50Hz) - *Charging speed varies between devices - **Please check your laptop specs for compatibility
Package contents	- USB-C Charger - 2m USB-C cable
System requirements	- 100-240V AC wall power socket

Marketing

Extended retailer text	You've got the power Phone down to the last 2%? Charge up in no time at all with this powerful 65W USB-C charger to ensure you've got enough power for whatever comes your way.
------------------------	---

Super and sustainable

The only thing better than a fast charger is one that’s sustainable too! With a composition of 75% recycled materials, the Maxo helps you power up with added peace of mind.

One charger fits all

If you’re tired of having multiple chargers to power each of your devices, the Maxo is the perfect fit for you – compatible with any device with a USB-C connection, you can charge your smartphone, tablet or laptop* – the choice is yours.

Go where you want

Enjoy working from your desk, sofa, or bed with the Maxo’s extra-long 2m USB-C cable which offers the freedom and flexibility to plug in wherever you like.

Internationally ideal

Keen travelers will find the Maxo the perfect travel companion thanks to its compatibility with all wall power socket voltages worldwide.

The best things come in small packages

Say goodbye to clunky chargers and hello to the small and sleek Maxo – specially designed to allow for a higher power output in a smaller form, this charger provides pocket-sized power.

Specifications

Plastic material	rPC
Sustainability method	PCR
Total weight	104 g
Weight of main unit	104 g
Height of main product (in mm)	56 mm
Width of main product (in mm)	28 mm
Depth of main product (in mm)	87 mm
Number of USB ports	1
Accessories	USB-C charge cable
Free Tip / Connector Service ava...	false

Cable length main cable	200 cm
Cables included	USB-C to USB-C
Protections	over-current over-heat over-load
Power plug type	UK
Power source	wall socket
Input power	100-240 VAC 50/60 1.7 A MAX
Charging technology	USB-C USB PD 3.0 + PPS
Max output amperes	3 A
Output voltage	5 9 12 15 20
Total max output power (W)	65 Watt
Power cable length	200 cm
Laptop voltage range	5 - 20 V
Compatible Device Types	laptop smartphone tablet

Main image

	25208_pictures_product_visual_1.tif ImageWidth: 5.000 px ImageHeight: 5.000 px ImageResolution: 300 dpi
---	---

Additional Product Images



25208_pictures_product_visual_2.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25208_pictures_product_top_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25208_pictures_product_top_2.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25208_pictures_product_front_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25208_pictures_product_side_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25208_pictures_product_extra_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi

Product Pictorials



25208_EN_pictures_product_pictorial_1.tif

ImageWidth: 4.000 px

ImageHeight: 4.000 px

ImageResolution: 300 dpi



25208_EN_pictures_product_pictorial_2.tif

ImageWidth: 4.000 px

ImageHeight: 4.000 px

ImageResolution: 300 dpi



25208_EN_pictures_product_pictorial_3.tif

ImageWidth: 4.000 px

ImageHeight: 4.000 px

ImageResolution: 300 dpi



25208_EN_pictures_product_pictorial_4.tif

ImageWidth: 4.000 px

ImageHeight: 4.000 px

ImageResolution: 300 dpi

Lifestyle Images



24817_pictures_lifestyle_visual_2.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_lifestyle_visual_1.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_productinuse_visual_1.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_productinuse_visual_2.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_productinuse_visual_3.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_productinuse_visual_4.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_productinuse_visual_5.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi



24817_pictures_productinuse_visual_6.jpg

ImageWidth: 4.000 px

ImageHeight: 3.000 px

ImageResolution: 300 dpi

Package Images



25208_pictures_package_visual_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25208_pictures_package_front_1.tif

ImageWidth: 1.510 px

ImageHeight: 1.996 px

ImageResolution: 300 dpi