

OMNITRONIC OD-4T Wall Speaker 100V white 2x

Weather-proof wall speaker pair (IP65) with 4" woofers and 30 W RMS

Art. No.: 11036915

GTIN: 4026397543575



List price: 95.08 €

incl. 19% VAT.

Features:

- 2-way system with 10 cm woofer (4") and 1.3 cm tweeter (0.5")
- Durable plastic cabinet with metal grille and cover for the connectors
- Power selector switch with 8 ohms operating position
- With panning and tilting mounting bracket for ceiling or wall installation in most varying angles
- Suitable for outdoor use IP65
- 2 pieces per set

Package contents

- 2 x compact cabinet speaker, 1 x user manual, 2 x mounting bracket, 4 x knurled screw

Logistic

EAN / GTIN: 4026397543575

Weight: 3,94 kg

Length: 0.33 m

Width: 0.15 m

Height: 0.21 m

Technical specifications:

IP classification:	IP65
Power:	Program: 60W (8 ohms) Rated: 30W RMS (8 ohms) Rated: 16W RMS (100V PA)
Frequency range:	100 - 20000 Hz
Sensitivity:	88 dB
Max. SPL:	100 dB (100V PA); 106 dB (8 ohms)
Dispersion angle:	170° x 170°
Impedance:	Public address systems 100V; 8 ohms

Attachment system:	Panning and tilting mounting bracket for ceiling or wall installation in most varying angles
Power tapping:	2W; 4W; 8W; 16W RMS via Selector switch switchable
Connections:	Input: speaker via screw terminal
Speaker:	1 x woofer 4" 1 x Calottes highs 0,5"
Type of speaker:	Compact cabinet speaker
Dimensions:	Width: 12,5 cm Depth: 12,5 cm Height: 19,5 cm
Weight:	3,66 kg