

## OMNITRONIC ODX-215TM Installation Speaker 100V dark gray

Weather-proof 15" wall speaker (IP56) with mount, 400 W RMS

Art. No.: 11036967

GTIN: 4026397703221



**List price: 1010.31 €**

incl. 19% VAT.

### Features:

- Well-balanced sound
- 2-way coaxial system with 38 cm woofer (15") and 4 cm tweeter (1.7")
- Power selector switch with 8 ohms operating position
- Screw terminals for parallel connection
- With Mounting bracket
- Grey aluminum grille
- Suitable for outdoor use IP56

#### Package contents

- 1 x top, 1 x mounting bracket, 1 x user manual, 6 x screw, 1 x safety eyelet, 1 x lid, 8 x washer

### Logistic

EAN / GTIN: 4026397703221

Weight: 29,90 kg

Length: 0.61 m

Width: 0.59 m

Height: 0.57 m

Bulky product

### Technical specifications:

IP classification:	IP56
Power:	Program: 800W Rated: 400W RMS
Frequency range:	50 - 18000 Hz
Sensitivity:	103 dB (1W/1m)
Max. SPL:	129 dB
Dispersion angle:	70° x 70°
Impedance:	8 ohms; Public address systems 100V
Attachment system:	Mounting bracket

Power tapping:	75W; 150W; 300W; 400W RMS via Selector switch switchable
Connections:	Input: speaker via screw terminal
Crossover frequency:	2100 Hz
Speaker:	1 x woofer 15" Basket material: aluminum Conematerial: Cardboard/paper Voice coil lows 3" 1 x compression tweeter highs 1" Voice coil compression tweeter highs 1,7"
Type of speaker:	On-ceiling/on-wall speaker
Color:	Grey
Dimensions:	Width: 50 cm Depth: 52 cm Height: 50 cm
Weight:	26,80 kg