

## OMNITRONIC WPS-6W PA Wall Speaker

2-way speaker with mount, Public address systems 100V, 40 W RMS

Art. No.: 80710533

GTIN: 4026397412192



**List price: 106.98 €**

incl. 19% VAT.

### Description:

The WPS series by OMNITRONIC convinces with its well thought-out package: apart from the undeniable neat looks, sound as well as functions are located on a high level. The 2-way systems, as the WPS-6W, are equipped with a multi-step potentiometer, an ABS plastic body with a metal safety guard and a pivotable mounting bracket. Due to the trapezoid construction, the fitting in corners is as easy as anything.

### Logistic

EAN / GTIN: 4026397412192

Weight: 4,15 kg

Length: 0.28 m

Width: 0.27 m

Height: 0.35 m

### Features:

- 2-way bass-reflex system for powerful bass
- Trapezoidal cabinet for corner installation
- With Mounting bracket
- Scratchproof and shockproof

#### Package contents

- 1 x device, 1 x user manual

### Technical specifications:

Power:	Program: 80W Rated: 40W RMS
Frequency range:	85 - 20000 Hz
Sensitivity:	88 dB (1W/1m)
Max. SPL:	105 dB

Impedance:	Public address systems 100V
Attachment system:	Mounting bracket
Power tapping:	5W; 10W; 20W; 40W RMS via Selector switch switchable
Connections:	Input: speaker via screw terminal
Speaker:	1 x woofer 6,5" PP polypropylene 1 x Tweeter PP polypropylene with wave guide
Type of speaker:	Compact cabinet speaker
Type of construction:	Vented
Material:	ABS Acrylonitrile butadiene styrene
Color:	White, scratchproof and shockproof
Dimensions:	Width: 21,5 cm Depth: 19 cm Height: 28,4 cm
Weight:	3,40 kg