Crimping tools

PZ 4 • PZ 6/5 Crimping tools for ferrules

- Ferrule insertion from the side
- Ratchet for precise crimping
- Ratchet release option in case of incorrect operation

PZ 3 Crimping tool for ferrules





PZ 4

Technical data

Lenath

Crimping tool for ferrules according to DIN 46228 part 1 and 4 with and without plastic collars from 0.5...4 mm² (~ AWG 20...12)

• Only one crimping profile for the entire cross-section range

200 mm



PZ 6/5

Technical data

Lenath

Crimping tool for ferrules according to DIN 46228 part 1 and 4 with and without plastic collars from 0.25...6 mm² (~ AWG 24...10)

- Crimp conforms to EN 60947-1
- Five crimping profiles for the rated conductor cross-sections
- Registration in accordance with VG 95211 (Military designation VG 95236 T 14 A 0001)



PZ 3

Technical data

Lenath

Crimping tool for ferrules according to DIN 46228 part 1 and 4 with and without plastic collars from 0.5...6 mm² (~ AWG 20...10)


- Ratchet for precise crimping
- Ratchet release option in case of incorrect operation

200 mm


- Only one profile for entire wire range
- Ferrule insertion from the front

Lengur	200 111111	Lengur	200 111111	Lengur	200 111111	
Weight	448 g	Weight	423 g	Weight	426 g	
Ordering data		Ordering data	Ordering data		Ordering data	
Туре	Cat. No.	Туре	Cat. No.	Type	Cat. No.	
PZ 4	9012500000	PZ 6/5	9011460000	PZ 3	0567300000	
Accessories		Accessories		Accessories		
Ferrules see pages 74 - 79		Ferrules see pages	Ferrules see pages 74 - 79		Ferrules see pages 74 - 79	

200 mm



PZ 6 roto **Crimping tools** for ferrules



PZ 16 • PZ ZH 16 Crimping tools for ferrules

- Ratchet for precise crimping
- Ratchet release option in case of incorrect operation
- Ferrule insertion from the side



PZ 6 roto

Technical data

Crimping tool for ferrules according to DIN 46228 parts 1 and 4 with and without plastic collars from 0.14 ... 6 mm² (~ AWG 26 ... 10)

- Ratchet for precise crimping
- Ratchet release option in case of incorrect operation
- Only one profile for entire wire range
- Rotatable crimp die for ferrule insertion from the front or the side



PZ 16

Technical data

Crimping tool for ferrules according to DIN 46228 parts 1 and 4 with and without plastic collars from 6...16 mm² (~ AWG 10 ... 6)

- Three crimping profiles for rated conductor cross-sections
- Crimp conforms to EN 60947-1
- Registration in accordance with VG 95211 (Military designation VG 95236 T 14 B 002)



PZ ZH 16

Technical data

Crimping tool for twin ferrules (requirement similar to DIN 46228 T.4) with plastic collars from 6...16 mm² (~AWG 10 ... 6)

- Three crimping profiles for rated conductor cross-sections
- Crimp conforms to EN 60947-1

reclinical data		i comincai data	recinical data		recinical data	
Length	200 mm	Length	200 mm	Length	260 mm	
Weight	428 g	Weight	418 g	Weight	700 g	
Ordering data		Ordering data	Ordering data		Ordering data	
Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	
PZ 6 roto	9014350000	PZ 16	9012600000	PZ ZH 16	9013600000	
Accessories		Accessories	Accessories		Accessories	
Ferrules see pages 74 - 79		Ferrules see pages	Ferrules see pages 74 - 79		Ferrules see pages 74 - 79	
	·			·	·	