Product data sheet

Specifications



Contactor, Type S, multipole lighting, mechanically held, 200A, 3 pole, 110/120VAC 50/60Hz coil, open style

8903SVO11V02

Product availability : Stock - Normally stocked in distribution facility

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	200 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	9.13 in (232 mm)
Depth	6.73 in (171 mm)
Width	5.98 in (152 mm)

Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21324-8903 S (NOT S*C) MECH.
Discount Schedule	CP1
GTIN	785901102502
Returnability	No
Country of origin	MX

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.70 in (24.638 cm)
Package 1 Width	13.70 in (34.798 cm)
Package 1 Length	17.80 in (45.212 cm)
Package 1 Weight	23.33 lb(US) (10.582 kg)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months

Recommended replacement(s)