
Product data sheet

Specifications



Contactor, Definite Purpose, 40A, 4 pole, 25 HP at 575 VAC, 3 phase, 277 VAC 60 Hz coil, open

8910DPA44V04

Product availability : Stock - Normally stocked in distribution facility

Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	40 A
Number of Poles	4P
Pole contact composition	4 NO
Range of Product	DPA

Complementary

Maximum Horse Power Rating	3 hp 115 V AC, 1 phase 7.5 hp 230 V AC, 1 phase 10 hp 230 V AC, 3 phase 20 hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Locked rotor rated current	240 A 277 V AC 200 A 460 V AC 160 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	277 V AC 60 Hz
Phase	3 phase
Electrical Connection	Box lugs Quick connect terminals

Environment

Product Certifications	UL Recognized CSA

Ordering and shipping details

Category	21344-8910 DPA 4_(40 AMP)
Discount Schedule	CP1B
GTIN	785901342717
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	4.20 in (10.668 cm)
Package 1 Weight	24.00 oz (680.389 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	7.20 in (18.288 cm)
Package 2 Width	6.90 in (17.526 cm)
Package 2 Length	8.50 in (21.59 cm)
Package 2 Weight	10.42 lb(US) (4.726 kg)

Offer Sustainability

REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months

Recommended replacement(s)