



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

BMXAMO0210H



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Mounting:	Any slot except 0
Isolation Between Channels:	750 VDC
Isolation Between Channels and Bus:	1400 VDC
UL & CSA:	Yes
CE:	Yes
RoHS:	Yes
Class 1 Div 2 CSA:	Yes
GOST/BV/GL/RMRS/ABS:	Yes
Weight [kg]:	0.144

Specification:

Description:	
Selection:	M340 PAC
Conf.Coating - 25C to 70C op.temp.:	Yes
Input Voltage Range:	
Input Current:	
Output Voltage Range:	± 10 V
Output Current:	1 to 20 mA, 4 to 20 mA
Connection Type:	BMXFTB2000/BMXFTB2010/BMXFTB2020/BMXFTW301/BMXFTW501/BMXFTW1001
Number of Inputs:	
Number of Outputs:	2