

Product data sheet

Specifications



Lexium 62 Single Drive 15 A - accessory kit included

LXM62DD15C21000

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	PacDrive 3
Product or Component Type	Single drive
Device short name	LXM 62

Complementary

Product compatibility	Servo motor SHS Servo motor SH3 2.76 in (70 mm), 2 optimized in terms of torque and speed Servo motor SH3 2.76 in (70 mm), 3 optimized in terms of torque and speed Servo motor SH3 3.94 in (100 mm), 1 optimized in terms of torque and speed Servo motor SH3 3.94 in (100 mm), 2 optimized in terms of torque and speed Servo motor SH3 3.94 in (100 mm), 2 optimized in terms of high torque Servo motor SH3 3.94 in (100 mm), 3 optimized in terms of high torque Servo motor SH3 5.51 in (140 mm), 1 optimized in terms of high torque Servo motor MH3 2.76 in (70 mm), 2 optimized in terms of torque and speed Servo motor MH3 2.76 in (70 mm), 3 optimized in terms of torque and speed Servo motor MH3 3.94 in (100 mm), 1 optimized in terms of torque and speed
-----------------------	--

Phase	Single phase Three phase
-------	-----------------------------

[Us] rated supply voltage (through power supply module)	230 V +/- 10 % 400 V +/- 10 %
--	----------------------------------

Supply frequency	50/60 Hz +/-5 %
------------------	-----------------

Continuous output current	5 A 4 kHz
---------------------------	-----------

Output current 3s peak	15 A 4 kHz
------------------------	------------

Continuous power	2.4 kW
------------------	--------

Nominal power	2.4 kW
---------------	--------

Overvoltage category	III
----------------------	-----

Electrical connection	Terminal 0.2...15 mm ² , AWG 24...AWG 16 CN4) Terminal 0.5...16 mm ² , AWG 20...AWG 6 CN5) Terminal 0.75...16 mm ² , AWG 18...AWG 6 CN6) Terminal 0.2...6 mm ² , AWG 24...AWG 10 CN7)
-----------------------	--

Tightening torque	CN1 22.13 lbf.in (2.5 N.m)
-------------------	----------------------------

Number of inputs	2 digital 2 touch probe
------------------	----------------------------

Discrete input voltage	24 V DC
------------------------	---------

Number of outputs	2 digital
-------------------	-----------

Discrete output voltage	24 V DC
-------------------------	---------

Safety function	STO (safe torque off)
-----------------	-----------------------

Physical interface	SERCOS III
Net Weight	6.61 lb(US) (3 kg)

Environment

Standards	CSA C22.2 No 14 EN 61800-5-1 EN/ISO 13849-1 EN/ISO 13849-2 UL 508C EN 62061 IEC 61508 IEC 62061 EN 61800-5-2 EN 61800-3
Product Certifications	CSA TÜV CE EAC UL
IP degree of protection	IP20 EN/IEC 60529
Vibration resistance	10 m/s ² EN/IEC 60721-3-3
Shock resistance	100 m/s ² EN/IEC 60721-3-3
Pollution degree	2 EN/IEC 61800-5-2
Environmental characteristic	3K3 IEC 60721-3-3
Relative humidity	5...85 %
Ambient Air Temperature for Operation	41...131 °F (5...55 °C)

Ordering and shipping details

Category	18356-PACDRIVE3 LEXIM62 SERVO DRIVES
Discount Schedule	PC52
GTIN	3606485317724
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.33 in (11 cm)
Package 1 Width	12.99 in (33 cm)
Package 1 Length	17.13 in (43.5 cm)
Package 1 Weight	8.44 lb(US) (3.828 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Recommended replacement(s)