

TRT034N

7 Day Digital Programmer – 1 Channel

Features & Benefits

- 7 day programming for use with room thermostat
- 3 timed control periods per day (5 day and 2 or 7 day programming).
- Programme copy function
- 1 and 2 and 3 hour boost function
- Holiday mode
- Always ON and OFF override mode
- Blue LED screen illuminates upon setting
- Automatic summer and winter changeover
- Change over contacts
- Factory fitted rechargeable battery backup



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C
Connection	3 Wire
Setting Type	Digital
Battery Type	3.6V 20mA Rechargeable
Power Reserve	1 Week (7 Days)
Program Modes	24 Hour/7 Day, Holiday Mode, 1,2 or 3 Hour Boost
Switch type	Single Pole, Double Throw (SPDT)

Data sheet

TRT034N

Climate / Programastat Plus

Mounting Hole Centres (mm)	60
Standby Consumption	<8W
Switch rating	3A Resistive, 1A Inductive
Shortest Switching Time	1 Minute
Programmable Slots	3 ON, 3 OFF
Cable Entry(s)	Back Entry

General

Weight (g)	194.2
Height (mm)	90
Width (mm)	135
Depth (mm)	30
Body Construction	Polycarbonate
Product Colour	White
Accessories (Included)	Rawl Plugs, Screws
EAN Number	5012483014400
Guarantee Period	3 Years
Trade Tariff Commodity Code	8536508090

Line Diagrams

