

TRT035N

7 Day Programmable Room Thermostat with Frost Protection

Features & Benefits

- 7 day time and temperature programming with digital accuracy
- 6 different time/temperature periods (5 day and 2 or 7 day programming)
- Easy +/- illuminated push button settings
- Programme copy function for quick and easy setting
- Easy view time and temperature display illuminates on setting
- Frost protection setting
- Temperature swing adjustment (using DIP switches) between a 0.5°C and 1°C
- Optimum start feature (up to temperature at the time the programme is due to start)
- Voltage free change over contacts
- Display battery powered using 2x AA batteries supplied



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C
Connection	2 Wire
Setting Type	Digital

Data sheet

TRT035N

Climate / Programastat Plus

Battery Type	x2 AA Batteries
Power Reserve	Depends on usage
Set Temperature Range	5°C to 35°C, User Adjustable
ErP Product Class	Class IV
Temperature Swing (Hysteresis)	1°C or 0.5°C
Optimum Start	Supported
Program Modes	24 Hour/7 Day, Frost Protection Mode
Switch type	Single Pole
Voltage Free Contacts	Normally Open, Normally Closed (Changeover)
Mounting Hole Centres (mm)	60
Standby Consumption	<01mW
Switch rating	3A Resistive, 1A Inductive
Programmable Slots	6 Programmed Temperature Periods (Per Day)
Cable Entry(s)	Back Entry

General

Weight (g)	192.9
Height (mm)	90
Width (mm)	135
Depth (mm)	30
Body Construction	Polycarbonate
Product Colour	White
Accessories (Included)	Rawl Plugs, Screws, x2 AA Batteries
EAN Number	5012483014417
Guarantee Period	3 Years
Trade Tariff Commodity Code	9032108090

Line Diagrams

