







This item includes:

			
Item No.: 221-412	Item No.: 221-413	Item No.: 221-415	Item No.: 221-2411
Splicing connector with levers; for all conductor types; max. 4 mm ² ; 2-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	Splicing connector with levers; for all conductor types; max. 4 mm ² ; 3-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	Splicing connector with levers; for all conductor types; max. 4 mm ² ; 5-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	Inline splicing connector with levers; for all conductor types; max. 4 mm ² ; 2-conductor; transparent housing; Transparent cover; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent

Material data	
Note (material data)	Information on material specifications can be found here
Fire load	5.642 MJ
Weight	412.1 g

Commercial data	
ETIM 8.0	EC000446
PU (SPU)	1 pcs
Country of origin	DE
GTIN	4066966194883
Customs tariff number	85369010000

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption



Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 887-803	