

DVD-USB-04

External USB DVD drive

- Archive your videos, photos, data and music to CD or DVD
- Compact design, perfect for use with laptops
- Silent operation



Features

- External CD/DVD reader/recorder with USB interface
- Enables rapid burning of CD/DVD media with 24x write speed for CD and 8x for DVD
- High-speed USB 2.0 interface for reliable use with transfer rates up to 480 Mbps
- Silent play, smart disc read speed control reduces operational noise.

Packaging

Q'ty in crtn, pcs	32
Crtn volume, CUM	0.0387
Crtn weight, kgs	14.64
Individual package size LxWxH:	46x189x162 mm
Carton size LxWxH:	430x450x200 mm
Country of origin	CN
Barcode	8716309125871
Customs code	8522900090

Package contents

DVD drive
USB data cable, 50 cm
USB power cable, 50 cm
User manual

Certificates



Specifications

Interface: USB 2.0

Power supply: 5 V DC up to 1 A

Maximum Read Speeds: 24x: CD-R, CD-RW, CD-ROM, CD-DA; 8x: DVD-ROM, DVD+/-R, DVD+/-RW, M-Disc; 6x: DVD-RAM; 4x: DVD-Video

Maximum Write Speeds: 24x: CD-R, CD-RW; 8x: DVD+/-RW, DVD+/-R; 6x: DVD-RW, DVD+/-R DL; 5x: DVD-RAM; 4x: M-Disc

Supports: CD-DA, CD-R, CD-RW, DVD+R, DVD+R DL, DVD+RW, DVD-R, DVD-R DL, DVD-RAM, DVD-ROM DL, DVD-RW, DVD-Video

Supported disc diameter: 80 mm, 120 mm

Dual Layer Media Supported: Yes

Dimensions: 137.5 x 135.5 x 17.5 mm

Net weight: 0.28 kg

Optical drive mechanics contain refurbished elements

System requirements

Windows 10/11

Two free USB ports (one for extra power)