

3/8"

BLACK

GREEN

GREY

BLUE

SIGNAL GREY

### 3093 K Plastic ratchet

3/8" square drive

For fast and easy tightening of bolted connections up to max. 70 N·m.

Very handy and compact, housing and handle form one unit. Made from sturdy compound material.

European Patent applied.

Dimensions: 44 x 145 x 39 mm.

Available in five colours.

Code	No.	Description	
6242090	3093 U-10 K SCHWARZ	Reversible ratchet 3/8" black	235
6244970	3093 U-10 K GRÜN	Reversible ratchet 3/8" green	235
6248100	3093 U-10 K GRAU	Reversible ratchet 3/8" grey	235
6248290	3093 U-10 K BLAU	Reversible ratchet 3/8" blue	235
1505394	3093 U-10 K SIGNALGRAU	Reversible ratchet 3/8" signal grey	235

DIN 3122, ISO 3315

3/8"

3093 Z-94

3093 U-3

3093 U-10

3093 U-20

3093 GZ-94

3093 GU-3

### 3093 Ratchets

3/8" square drive

For hand-operated sockets and accessories with square drive as per DIN 3120 - C 10, ISO 1174 ball locking device. GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated.

- 3093 Z-94  $\sphericalangle$  10° Ratchet with square coupler, medium toothed, very robust.
- 3093 U-3  $\sphericalangle$  5° Reversible ratchet with disc change, fine toothed.
- 3093 U-10  $\sphericalangle$  11° Reversible ratchet with lever change, push button release, locks in middle position, oval head.
- 3093 U-20  $\sphericalangle$  6° Reversible ratchet with lever change, push button release, locks in middle position, oval head, dual-material handle, non-slip, hanging hole.
- 3093 GZ-94  $\sphericalangle$  10° Flexible head ratchet with square coupler, swivels through 180°, medium toothed, max. torque 200 N·m.
- 3093 GU-3  $\sphericalangle$  5° Flexible head reversible ratchet, swivels through 180°, with joint lock, fine toothed, max. torque 200 N·m.

Code	No.	Description	L mm	H mm	
6237680	3093 Z-94	Ratchet handle with coupler 3/8"	200	18,0	220
6237090	3093 U-3	Reversible ratchet 3/8"	200	32,0	200
6236950	3093 U-10	Reversible ratchet 3/8"	200	30,2	250
1556800	3093 U-20	Reversible ratchet, lever change 3/8"	200	30,0	320
6237330	3093 GZ-94	Flexible head ratchet 3/8"	282	32,0	330
6237170	3093 GU-3	Flexible head ratchet 3/8"	282	20,0	350