



**IKS 19 PZD Screwdriver bit socket for cruciform head screws POZIDRIV**

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 12.5, ISO 1174 with ball retaining groove, knurled grip. Chrome-plated, bit as per DIN ISO 8764-1 PZ, in GEDORE vanadium special steel, gun-metal finish.

Code	No.	L	t	⚙️
6156680	IKS 19 PZD 2	60	22	80
6156760	IKS 19 PZD 3	60	22	80
6156840	IKS 19 PZD 4	60	22	80



**IN 19 Screwdriver bit socket for hexagon head screws**

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 12.5, ISO 1174 with ball retaining groove, knurled grip. Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

**IN 19 17** for oil filter and drain plug screws. \* not standardised

Code	No.	⌀mm	L	d	t	⚙️
6153070	IN 19 4*	4	60	22,5	22	45
6153150	IN 19 5*	5	60	22,5	22	50
6153230	IN 19 6	6	60	22,5	22	55
6153310	IN 19 7	7	60	22,5	22	58
6153580	IN 19 8	8	60	22,5	22	60
6153660	IN 19 9*	9	60	22,5	22	63
6153740	IN 19 10	10	60	22,5	22	65
6153820	IN 19 12	12	60	23,0	22	75
6153900	IN 19 14	14	60	24,7	20	85
6154040	IN 19 17*	17	60	28,0	20	115
6154120	IN 19 19*	19	60	27,0	20	120

  

Code	No.	⌀AF	L	d	t	⚙️
6154710	IN 19 3/16AF	3/16	60	22,5	22	50
6154980	IN 19 7/32AF	7/32	60	22,5	22	53
6155010	IN 19 1/4AF	1/4	60	22,5	22	55
6155280	IN 19 9/32AF	9/32	60	22,5	22	58
6155360	IN 19 5/16AF	5/16	60	22,5	22	60
6155440	IN 19 3/8AF	3/8	60	22,5	22	65
6155520	IN 19 1/2AF	1/2	60	23,0	22	80
6155600	IN 19 9/16AF	9/16	60	24,7	20	85
6155790	IN 19 5/8AF	5/8	60	28,0	20	115



**IN 19 L Screwdriver bit socket long, for hexagon head screws**

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 12.5, ISO 1174 with ball retaining groove, knurled grip. Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

\* stepped hexagon bit t = 13 mm \* not standardised

Code	No.	⌀mm	L	d	t	⚙️
6162060	IN 19 L 5-90*	5	90	22,5	13 / 52	75
6157140	IN 19 L 5-180*	5	180	22,5	13 / 142	150
6157300	IN 19 L 6-90	6	90	22,5	52	70
6145800	IN 19 L 6-140	6	140	22,5	13 / 102	90
6145990	IN 19 L 6-160	6	160	22,5	13 / 122	120
6157570	IN 19 L 7-100	7	100	22,5	62	100
6157730	IN 19 L 8-90	8	90	22,5	52	75
6157810	IN 19 L 8-120	8	120	22,5	82	20
6158110	IN 19 L 10-140	10	140	22,5	102	130
6158460	IN 19 L 12-140	12	140	23,0	102	155
6158620	IN 19 L 14-140	14	140	24,7	100	190



**IN 19 LK Screwdriver bit socket long, with ball end for hexagon head screws**

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 12.5, ISO 1174 with ball retaining groove, knurled grip. Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

Code	No.	⌀mm	L	d	t	⚙️
6162810	IN 19 LK 6-140	6	140	22,5	102	80
6165080	IN 19 LK 7-140	7	140	22,5	102	90
6165160	IN 19 LK 8-140	8	140	22,5	102	100
6166800	IN 19 LK 10-140	10	140	22,5	102	150
6172370	IN 19 LK 12-140	12	140	23,0	102	190