

24VDC 2A UK Power Supply



TIGER PART: TP2448

Features:

- Supplied with fixed UK pins
- Universal 100-240vac input voltage
- Level VI efficiency
- Approved to latest EN62368-1 safety standard
- CE marked and confirms with UKCA requirement



Part number:	TP2448
Input voltage:	100-240vac (90-264vac max.)
Input frequency:	47 - 63Hz
Output voltage:	24vdc
Current:	2000mA (2 amp)
Power :	48 Watts
Protection:	Short Circuit, Over voltage
Dimensions:	97 x 45 x 35mm
Cord length:	1.5 metres
DC connector:	2.5 x 5.5 x 12mm (Female) Right Angle (90 degree)
Polarity:	+ve (positive) centre
Leakage current:	<0.25mA
Operating temperature:	0°C to + 40°C

TIGER POWER PRODUCTS – QUALITY & RELIABILITY

This specification is not for general release or circulation. Tiger Power reserves the right to make changes to spec. or product without notice or liability.