



## 12V 16.67A 200W LONG LIFE LED DRIVER

Super slim LED driver providing a constant voltage 12Vdc regulated output at up to 8.33A 100W. No minimum load so it can be used for any power rating up to 100W. SELV. Open circuit, short circuit, overload and auto recovery. Class II, lifetime 30,000hrs.



### ·Input

Items	Conditions	Request	Note
Input voltage	Ta	220-240Vac	--
Input frequency		50/60Hz	--
Input current	25°C, rated input voltage, output with max. rated power	<0.3A	--
Input power		<16W	--
Efficiency		≥85%	--
Standby	25°C, rated input voltage, output without load	<0.5W	average
Inrush current	25°C, rated input voltage	<60A	peak
PF	25°C, rated input voltage, output max. rated power	≥0.90	--

### ·Temperate and others

Item	Conditions	Request	Note
Operation temp.	--	-20-45°C	--
Relative humidity	--	45%-85%	--
Max. case temp.	--	85°C	--
Lifetime	Max. Ta, rated input voltage, output with max. rated power	30,000hr	--
Working noise	25°C, rated input voltage, output with rated power, mute box background noise <35dB, pickup 10cm distance from products	yes	--

### ·Protection

Items	Conditions	Request	Note
Open circuit	Ta, rated input voltage, no load	"--"	--
Over load	Ta, 0.94-1.06 times of input voltage, 1.5 times of rated power	yes	--
Short circuit	Ta, 0.94-1.06 times of input voltage	yes	--
			--
Over voltage	Ta, 0.94-1.06 times of input voltage, output voltage is 1.5 times of rated one	yes	--
Auto recovery	Over load, short circuit recovation	yes	--
			--

### ·Output

Items	Conditions	Request	Note
Startup time	25°C, rated input voltage, output with max. rated power	<0.5s	--
Output voltage and precision	Ta, rated input voltage, output with rated power	12V±5%	--
Output current range	Ta, rated input voltage	0-8.33A	
Output voltage wave	25°C, rated input voltage, output with max. rated power	120mV	Vp-p
Output overload	25°C, rated input voltage, output with 2 times LED load	yes	--
Output current and precision	Ta, rated input voltage, output with rated power	--	--
Rated output voltage range	Ta, rated input voltage,	--	--
Output current wave	25°C, rated input voltage, output with max. rated power	--	Ip-p
Dimming mode	--	--	--
Dimming range	--	--	--

### ·Mechanical, mounting

Items	Conditions
Case material and size	Plastic case 205mm × 71mm × 35mm
Mounting ways	Independent
Insulation type	Class II
IP grade	IP20
Input connection	screw terminals
Output connection	screw terminals


### ·Standard

Items	Conditions
Safety	IEC61347-1, IEC61347-2-13
Harmonic	IEC61000-3-2
EMI	IEC55015
EMS	IEC61547

**TIGER POWER PRODUCTS – QUALITY & RELIABILITY**

12V 16.67A 200W  
LONG LIFE LED DRIVER

TGR-12V-200W



Please note the output is provided via 2 sets of terminal blocks. Each + and - set is capable of providing up to 10A (120W) max, with the total load of 16.67A (200W) only possible when using both + + and - - output terminals

Refer to above markings and name plate and please contact us with any questions