



HONEYWELL PART NUMBER
11SM1777-T
PRODUCT CODE TWY3040

REV	DOCUMENT	CHANGED BY	CHECK
4	0038444	KVS 09APR08	ASD



NOTE -

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - MATING CONTACT SURFACES ARE OVERLAYS OF 24K SOLID GOLD AND GOLD ALLOY
- 4 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.	PR - 6487
REPLACES	X65439 - SM

CHARACTERISTICS
OPERATING FORCE - - 56 GRAM MAX
RELEASE FORCE - - - 14 GRAM MIN
DIFFERENTIAL TRAVEL - - - .002 MAX
OVERTRAVEL - - - - - .005 MIN

ELECTRICAL DATA
CONTACT ARRANGEMENT SPDT
APPROVALS UL, CSA 0.1A 125 VAC 30 VDC BRAND L171

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION

DRAWN	VK	14 FEB 08
CHECK	RJ	14 FEB 08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	11SM1777-T	4
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1