



VT-11020S 17W LED WALL LIGHT WITH SENSOR
4000K WHITE BODY IP65



FEATURES

- Well-designed 350° beam angle adjustable wall light with Sensor
- Fitted with high quality LEDs for better reliability
- Stylish, Modern Design-beautiful, and energy saving
- Efficient LED driver and intruded heat sink for longer lifespan
- PIR Sensor with a sensing distance of 10 Meter
- Suitable for decor, restaurants, residential, facades etc.

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	4000K
Model:	VT-11020S-W
Watts:	17
Lumens:	2580
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	212x165x100mm
On/Off Cycles:	>15000
Hold Time:	30sec to 3min adjustable
LED Chip Type:	SMD
Beam Angle:	350°
Detection Distance:	10 Meters
CRI:	>80
Energy Rating Label:	E (2021)
IP Rating:	IP65
Long Life:	20,000 Hours
Sensor Type:	PIR



LISTING DETAILS

SKU:	2939
Model:	VT-11020S-W
EAN:	3800157689489
Commodity Code:	9405423990

PACKAGING

Gross Weight (Kgs):	1.5
Unit CBM:	0.00642
Dimension:	212x165x100mm

MASTER BOX PACKAGING

Box Qty:	12
Qty Per Pallet:	216
Length (Box) mm:	230
Width (Box) mm:	125
Height (Box) mm:	190