



VT-2420 288W LED RGB CONTROLLER WITH 20 KEY RF REMOTE CONTROL



TECHNICAL INFORMATION

Model:	VT-2420
Input Power:	DC:12V/24V
Dimension:	91x88x24mm
IP Rating:	IP20

IP20
STANDARD

FEATURES

- 20 Key RF wireless remote controller
- Comes with 3 output channels
- Maximum current of <8A(each channel)
- DC:12V - Load <288W | DC:24V - Load <576W
- Easy to Install
- Compatible with V-TAC Striplights

LISTING DETAILS

SKU:	3339
Model:	VT-2420
EAN:	3800157634625
Commodity Code:	85437090

PACKAGING

Gross Weight (Kgs):	0.238
Unit CBM:	0.0005
Dimension:	91x88x24mm

MASTER BOX PACKAGING

Box Qty:	60
Qty Per Pallet:	1560
Length (Box) mm:	50
Width (Box) mm:	100
Height (Box) mm:	100