



VT-4005E 30W/40W/50W LED BATTEN FITTING EMERGENCY BATTERY 5FT SAMSUNG CHIP CCT 3IN1 135LM/W



FEATURES

- 3IN1 Color Changeable Batten fitting with Emergency backup
- 30W/40W/50W 3 Power selectable using DIP switch, 3 Color Changeable using DIP switch
- Fitted with high efficiency Samsung LED Chips
- Emergency backup for more than 3 Hours
- Batten Fitting designed with Lumen efficiency 135LM/W
- Strong and sturdy PC+Iron built with IK protection IK08
- Suitable for commercial lighting, office, supermarkets, shop, hotels & similar environment

TECHNICAL INFORMATION

Color Temperature:	3IN1
Model:	VT-4005E
Watts:	50
Lumens:	6750
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	PC+Iron
Dimension:	1470x65x70mm
Battery Charging Current:	30-400mA
Battery Discharge Current:	350-700mA
Working Time:	>3 Hours
PF:	>0.95
LED Chip Type:	SMD-Samsung Chip
Beam Angle:	120°
Battery Type:	6.4V, LiFePO4, 18730 2000mAh
CRI:	>80
Energy Rating Label:	D (2021)
IP Rating:	IP20
Long Life:	50,000 Hours
IK Rating:	IK08
Charging Time:	>12 Hours
lumens per watt:	135
Samsung:	Yes



LISTING DETAILS

SKU:	7017
Model:	VT-4005E
EAN:	3800157699150
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	1.98
Unit CBM:	0.010466
Dimension:	1470x65x70mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	
Length (Box) mm:	1480
Width (Box) mm:	70
Height (Box) mm:	77

