



VT-4006S 40W/50W/60W LED BATTEN FITTING SENSOR 6FT SAMSUNG CHIP CCT 3IN1 135LM/W



FEATURES

- 3IN1 Color Changeable Batten fitting with Sensor
- 40W/50W/60W 3 Power selectable using DIP switch, 3 Color Changeable using DIP switch
- Fitted with high efficiency Samsung LED Chips
- Batten Fitting designed with Lumen efficiency 135LM/W
- Strong and sturdy PC+Iron built with IK protection IK08
- Suitable for commercial lighting, office, supermarkets, shop, hotels & similar environment
- Compatible with SKU 7814

TECHNICAL INFORMATION

Color Temperature:	3IN1
Model:	VT-4006S
Watts:	60
Lumens:	8100
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	PC+Iron
Dimension:	1770x65x70mm
Detection Range:	12M (Max)
Time Delay:	15 mins/+∞
Ambient Light:	30 Lux/Disable
Hold Time:	5s/1 min/3 min/10 min
PF:	>0.95
LED Chip Type:	SMD-Samsung Chip
Beam Angle:	120°
Detection Angle:	Side Wall <150° Ceiling Mount 360°
Detection Distance:	50%/100%
CRI:	>80
Energy Rating Label:	D (2021)
IP Rating:	IP20
Long Life:	50,000 Hours
Sensor Type:	Microwave Sensor
IK Rating:	IK08
lumens per watt:	135
Samsung:	Yes



LISTING DETAILS

SKU:	7020
Model:	VT-4006S
EAN:	3800157699181
Commodity Code:	8539319090

PACKAGING

Gross Weight (Kgs):	2.03
Unit CBM:	0.011766
Dimension:	1770x65x70mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	
Length (Box) mm:	1780
Width (Box) mm:	70
Height (Box) mm:	77

