



VT-44003 300W SMD FLOODLIGHT SAMSUNG CHIP 1M WIRE 4000K BLACK BODY GREY GLASS 135LM/W



FEATURES

- Product designed with high lumen efficiency of 135 LM/W
- High quality LED SMD-Samsung Chip
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	4000K
Model:	VT-44003-B
Watts:	300
Lumens:	34440
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	496x49x445mm
Operation Temperature:	-20°C to +45°C
Instant Start:	0-100% in <1s
LED Chip Type:	SMD-Samsung Chip
Beam Angle:	115°
CRI:	>70
Energy Rating Label:	D (2021)
IP Rating:	IP65
Long Life:	25,000 Hours
Energy Saving:	85 Energy
Wire Length:	1m
lumens per watt:	135
Samsung:	Yes



IP65
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	10367
Model:	VT-44003-B
EAN:	3800170204362
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	4.69
Unit CBM:	0.01575
Dimension:	496x49x445mm

MASTER BOX PACKAGING

Box Qty:	2
Qty Per Pallet:	
Length (Box) mm:	500
Width (Box) mm:	55
Height (Box) mm:	450

