



VT-60024 24W BACKLIT SURFACE MOUNTED  
PANEL 4000K RD



FEATURES

- Strong and sturdy body Backlit Mini Panels
- High quality power driver ensures reliable lifetime
- Designed with high efficiency LED SMD chips.
- No Lead or Mercury content hence Environment friendly
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	4000K
Model:	VT-60024-RD
Watts:	24
Lumens:	2640
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	Day White
Dimension:	288.6x31.2mm
Operation Temperature:	-20°C to +45°C
On/Off Cycles:	>15000
Shape:	Round
LED Chip Type:	SMD
CRI:	>80
Energy Rating Label:	E (2021)
IP Rating:	IP20
Long Life:	20,000 Hours
Energy Saving:	85 Energy



IP20  
STANDARD

02  
YEAR  
WARRANTY

LISTING DETAILS

SKU:	7880
Model:	VT-60024-RD
EAN:	3800170201910
Commodity Code:	9405110000

PACKAGING

Gross Weight (Kgs):	0.49
Unit CBM:	0.003718
Dimension:	288.6x31.2mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	360
Length (Box) mm:	300
Width (Box) mm:	35
Height (Box) mm:	300