



VT-6436CCT 36W LED BACKLIT PANEL

595x595MM 3 SWITCH CCT 120LM/W



FEATURES

- TP(a) rated Diffuser to meet fire safety standards
- CCT Changeable with DIP Switch
- Highly efficient LIFUD Driver
- Powerful LED light source with lumen efficiency of 120LM/W
- IP40 for Panel and IP20 for Driver
- Flicker Free and No UV Radiation
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc

TECHNICAL INFORMATION

Output Voltage:	DC:33-40V
Color Temperature:	3IN1
Model:	VT-6436CCT
Watts:	36
Lumens:	4320
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	Aluminium+TPA(PC)
Dimension:	595x595x34mm
Operation Temperature:	-20°C to +40°C
Instant Start:	0-100% in < 1s
On/Off Cycles:	>15000
PF:	>0.9
LED Chip Type:	SMD
Beam Angle:	110°
CRI:	>80
Energy Rating Label:	E (2021)
IP Rating:	IP40
Long Life:	30,000 Hours
Driver Brand:	LIFUD
lumens per watt:	120



IP40
STANDARD

05 YEAR
WARRANTY

Super Bright
120
LUMENS/W

LISTING DETAILS

SKU:	6972
Model:	VT-6436CCT
EAN:	3800157698269
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	2.43
Unit CBM:	0.019489
Dimension:	595x595x34mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	30
Length (Box) mm:	628
Width (Box) mm:	270
Height (Box) mm:	665