



# VT-6448CCT 48W LED BORDERLINE PANEL 595x595MM 3IN1 WITH TERMINAL BOX



## FEATURES

- Stylish, Modern Design-beautiful LED Bordering Panel
- Powerful LED light source with lumen efficiency of LM/W
- 3IN1 CCT Changeable using DIP Switch
- Strong and sturdy body
- Fitted with high efficiency SMD LED Chips
- Highly efficient LIFUD Driver
- Easy to connect driver for quicker installation
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

## TECHNICAL INFORMATION

Dimmable:	No
Output Voltage:	DC:30-40V
Color Temperature:	3IN1
Model:	VT-6448CCT
Watts:	48
Lumens:	4800
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	3IN1
Dimension:	595x595mm
Operation Temperature:	-20°C to +40°C
Instant Start:	0-100% in < 1s
On/Off Cycles:	>15000
PF:	>0.9
LED Chip Type:	SMD
Beam Angle:	110°
CRI:	>80
Energy Rating Label:	F (2021)
IP Rating:	IP20
Long Life:	30,000 Hours
Driver Brand:	LIFUD
lumens per watt:	100



IP20  
STANDARD

05  
YEAR  
WARRANTY

Super Bright  
100  
LUMENS/W

## LISTING DETAILS

SKU:	10336
Model:	VT-6448CCT
EAN:	3800170207202
Commodity Code:	

## PACKAGING

Gross Weight (Kgs):	1.1
Unit CBM:	0.014291
Dimension:	595x595mm

## MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	
Length (Box) mm:	
Width (Box) mm:	
Height (Box) mm:	