



VT-767-2 1.5W LED SOLAR WALL LIGHT 4000K - WHITE +BLACK BODY



FEATURES

- Uses mono-crystalline solar panels for efficient photo voltaic conversion and lengthy lifespan
- PIR sensor for automatic switching on and switching off
- Easy to install, requires no wiring
- Robust and durable ABS plastic body
- Dust, heat and water resistant
- Renewable energy source: Solar powered
- Available range: 1.5W to 6.8W
- Suitable for gardens, pathways, garages etc.

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	4000K
Model:	VT-767-2-W
Watts:	1.5
Lumens:	220
Unit Color:	White+Black
Color for Web:	Day White
Body Type:	ABS + PC
Dimension:	144.5x96x79mm
Operation Temperature:	-25°C to +50°C
Detection Range:	2.6m
Working Time:	Maximum 24 Hours
No. Of Led:	14
LED Chip Type:	SMD
Beam Angle:	90°
Battery Type:	3.7V Lithium Battery 1200mAh
IP Rating:	IP65
Charging Time:	6-7 Hours Sunlight Charging

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

ROHS Certificate: [Check the certificate](#)

IP65
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	8276
Model:	VT-767-2-W
EAN:	3800157627931
Commodity Code:	94054131

PACKAGING

Gross Weight (Kgs):	0.266
Unit CBM:	0.00288
Dimension:	144.5x96x79mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	760
Length (Box) mm:	240
Width (Box) mm:	150
Height (Box) mm:	85