



VT-8-10 10W LED GRILL FITTING 30CM SAMSUNG CHIP 4000K



FEATURES

- Prismatic Fitting designed with Lumen efficiency 120LM/W
- Fitted with high efficiency SMD-Samsung Chip that offer up to 85% in energy savings
- Ballast or Starter not required, direct AC Power
- Long life span, low maintenance and energy saving
- No flickering, No UV radiation
- Applications - Residential, Hotels, Malls, Office and many more

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	4000K
Model:	VT-8-10-N
Watts:	10
Lumens:	1200
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	Day White
Body Type:	Plastic
Dimension:	300x75x24mm
Instant Start:	0-100% in <1s
On/Off Cycles:	>15000
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
Beam Angle:	120°
CRI:	>80
Downward LOR (%):	97.7
Upward LOR (%):	2.3
Energy Rating Label:	E (2021)
IP Rating:	IP20
Long Life:	25,000 Hours
Energy Saving:	85 Energy
Flicker Free:	flicker-free
lumens per watt:	120
Samsung:	Yes



LISTING DETAILS

SKU:	20345
Model:	VT-8-10-N
EAN:	3800157663670
Commodity Code:	9405114090

PACKAGING

Gross Weight (Kgs):	0.16
Unit CBM:	0.000833
Dimension:	300x75x24mm

MASTER BOX PACKAGING

Box Qty:	30
Qty Per Pallet:	1350
Length (Box) mm:	325
Width (Box) mm:	78
Height (Box) mm:	26

