



VT-8-60 60W LED GRILL FITTING 180CM SAMSUNG CHIP 4000K



FEATURES

- Prismatic Fitting designed with Lumen efficiency 120LM/W
- Fitted with high efficiency SMD-Samsung Chip LED Chips that offer up to 85% in energy savings
- 50% less power consumption compared to traditional grill fitting lighting
- Switch cycles: >15000
- Instant start-up in less than 0.5 second
- Applications - Residential, Hotels, Malls, Office and many more

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	4000K
Model:	VT-8-60-N
Watts:	60
Lumens:	7200
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	Day White
Body Type:	Plastic
Dimension:	1800x24x75mm
Instant Start:	0-100% in < 1s
On/Off Cycles:	>15000
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
Beam Angle:	120°
CRI:	>80
Energy Rating Label:	E (2021)
IP Rating:	IP20
Long Life:	25,000 Hours
Energy Saving:	85 Energy
lumens per watt:	120
Samsung:	Yes



LISTING DETAILS

SKU:	21670
Model:	VT-8-60-N
EAN:	3800157693684
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	0.66
Unit CBM:	0.00463
Dimension:	1800x24x75mm

MASTER BOX PACKAGING

Box Qty:	30
Qty Per Pallet:	
Length (Box) mm:	1845
Width (Box) mm:	80
Height (Box) mm:	26