



**VT-885 5W SPOTLIGHT FIRE RATED FITTING
SAMSUNG CHIP 3000K NICKLE**



FEATURES

- Fire-rated to resistance of 30,60,90 Mins
- Efficient replacement for traditional downlight fittings
- Swift connection - Quick Connector included
- Fitted with high efficiency Samsung LED Chips that offer up to 80% in energy savings
- Insulation Coverable
- Robust Iron build
- IP65 Protected for Outdoor use
- Spring Clips for safer installation and easy Maintenance
- Suitable for living rooms, bedrooms, utilities, corridors etc

TECHNICAL INFORMATION

Dimmable:	Yes
Color Temperature:	3000K
Model:	VT-885-N-N
Watts:	5
Lumens:	500
Input Power:	AC:220-240V, 50Hz
Unit Color:	Satin Nickle
Color for Web:	Warm White
Body Type:	Iron
Dimension:	81.5x57mm
Cutting Size:	57mm
On/Off Cycles:	>20000
Shape:	Round
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
Beam Angle:	70°
CRI:	>80
IP Rating:	IP65
Long Life:	30,000 Hours
Samsung:	Yes

IP65
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	218173
Model:	VT-885-N-N
EAN:	3800157676915
Commodity Code:	8539520000

PACKAGING

Gross Weight (Kgs):	0.23
Unit CBM:	0.001089
Dimension:	81.5x57mm

MASTER BOX PACKAGING

Box Qty:	60
Qty Per Pallet:	
Length (Box) mm:	110
Width (Box) mm:	90
Height (Box) mm:	110