



VT-COB 280 10W LED COB STRIP LIGHT WITH 4000K IP20 24V



FEATURES

- Stable technology for better reliability and longer lifespan
- 5M Roll quantity
- CRI>80 witness true to life colors
- IP20 Ingress protection
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation

TECHNICAL INFORMATION

Color Temperature:	4000K
Model:	VT-COB 280-N
Color for Web:	Day White
Dimension:	8mm
Beam Angle:	120°
Watts per meter:	10
LED Qty per meter:	288
CRI:	>80
Energy Rating Label:	F (2021)
IP Rating:	IP20
Roll Qty:	5M



IP20
STANDARD

LISTING DETAILS

SKU:	212653
Model:	VT-COB 280-N
EAN:	3800170206458
Commodity Code:	94054290

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000122
Dimension:	8mm

MASTER BOX PACKAGING

Box Qty:	400
Qty Per Pallet:	9600
Length (Box) mm:	155
Width (Box) mm:	180
Height (Box) mm:	10