



VT-2386 6W G45 LED FILAMENT BULB-CLEAR GLASS 2700K E27(130LM/WATT)



FEATURES

- Modern Clear filament Filament technology for better reliability and durability
- Replaces 60W watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps.
- Designed for E27 standard holder
- High color rendering index CRI >80
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	2700K
Model:	VT-2386
Watts:	6
Lumens:	800
Input Power:	AC:200-240V, 50Hz
Equivalence Watts:	60W
Unit Color:	Transparent
Color for Web:	Warm White
Body Type:	Glass
Dimension:	45x72mm
Operation Temperature:	-20°C to +45°C
On/Off Cycles:	>15000
Base:	E27
Shape:	G45
PF:	>0.5
LED Chip Type:	Filament
Beam Angle:	300°
CRI:	>80
Energy Rating Label:	E (2021)
IP Rating:	IP20
Long Life:	20,000 Hours
Energy Saving:	85 Energy
lumens per watt:	130



IP20
STANDARD

02
YEAR
WARRANTY

Super Bright
130
LUMENS/W

LISTING DETAILS

SKU:	2851
Model:	VT-2386
EAN:	3800157659291
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000196
Dimension:	45x72mm

MASTER BOX PACKAGING

Box Qty:	100
Qty Per Pallet:	5400
Length (Box) mm:	45
Width (Box) mm:	45
Height (Box) mm:	75