

FLOOR-8ABK

8" Floor and Wall Mount Active Subwoofer

Increasingly, high sound quality is required even in previously not-so-performing sound systems. Bars, restaurants, pubs, stores today use sound-music, video games, home cinema, etc. - not only as a simple background, but as a real marketing tool, where sound quality is an important ingredient.

These subwoofers are meant to be placed in confined spaces, under sofas or against walls. But despite their slim look, housing volume and high-excursion woofers, deliver truly worthy bass of much larger systems.

The built-in Class-AB amplifier is stable, designed for long-term use and equipped with an auto-power function (to reduce power consumption), limiter, thermal and overload protection.. In addition to the stereo line input, there is also a stereo high-power (low-impedance) input that allows direct connection to amplifier outputs or speakers of an existing system, which is very practical if distances or other factors do not allow traditional connections to the mixer or link outputs of an amplifier.

The subwoofers come with 4 rubber feet to help distance the speaker when placed with the woofer toward the floor and 2 brackets for suspended wall mounting to minimize the space and make the woofer fully protected as it faces the wall.



PRODUCT DETAILS

Key features

Bass-Reflex 8" Powered Subwoofer

Designed for Floor or Wall-Mount Use (Feet and Bracket included)

Class-AB Amplifiers with or 100W Power

Stereo Line Inputs and Stereo High-Level Inputs

Adjustable Crossover Frequency from 40Hz to 150Hz

Slim, stylish yet Rugged Housing with Black Finish

Specifications

Description	8" Floor & Wall Active Subwoofer
Speaker Type	Bass-Reflex Subwoofer
Frequency Response (-10 dB)	From 40 Hz to 500Hz
MAX SPL (1W@1m)	81dB
Crossover Frequency	40Hz - 150Hz
Crossover Filter Slope	18dB/Octave
Nominal Impedance	4ohm
Woofer Cone Diameter	8"
Amp Class	Class-AB
AES Power Rating	50Watt
Peak Power	100Watt
Protection	Short Circuit, Overload, Thermal, Limiter
Input Connections	Stereo Line Inputs (RCA), Hi-Level Stereo Inputs (Spring Speaker Terminal)
Power Connector	VDE Socket with Fuse
Level Control	Sub Level control
Phase Control	Switch 0°-180°
Auto Power	2-way Selector (AUTO, ON)
Power Requirement	230Vac (+/- 10%) - 50Hz
Max Power Consumption	110Watt
Housing Material	MDF, Black Finish
Housing Dimension (WxHxD)	540 x 158 x 400 mm
Subwoofer Weight	10 kg
Packing Size (WxHxD)	635 x 455 x 200 mm
Gross Weight	11 kg