

## Description

MG Chemicals line of swabs are offered in chamois, cotton, and foam tips. The swabs are designed with a round, tapered, or rectangular tip shape that are suited for all general and precision cleaning applications.

## Applications & Usages

The chamois are ideal for cleaning sensitive tape, audio, and optical heads. The cotton and foam swabs are designed for cleaning equipment, removing flux residues, applying adhesives, and absorbing chemical residues.

## Benefits and Features

- **ESD safe**—Cat No. 812AS
- **Non-abrasive**
- **100 ppi medical grade head**—Cat No. 812 and 8113
- **Low to zero lint and residue free**
- **Can be used with IPA (isopropyl alcohol) or DI (distilled) water**

## Product Details

<i>Cat No.</i>	<i>Overall Length</i>	<i>Tip Length</i>	<i>Handle Length</i>	<i>Handle Material</i>	<i>Tip End</i>	<i>Quantity per Bag</i>
<b>Chamois Swab</b>						
 810-15	4"	0.9"	3.2"	Plastic	Single	15
810-50	4"	0.9"	3.2"	Plastic	Single	50
810D-15	5"	0.9"	3.2"	Plastic	Double	15
810D-50	5"	0.9"	3.2"	Plastic	Double	50
<b>Double Headed Cotton Swab</b>						
 811-100	6"	0.5"	5"	Wood	Double	100
<b>Foam Over Cotton Swab</b>						
 812-10	6"	0.5"	5.5"	Wood	Single	10
812-50	6"	0.5"	5.5"	Wood	Single	50
812-250	6"	0.5"	5.5"	Wood	Single	250
812-1000	6"	0.5"	5.5"	Wood	Single	1 000
<b>Anti-Static Foam Over Cotton Swab</b>						
 812AS-10	6"	0.8"	5.3"	Wood	Single	10

Cat No.	Overall Length	Tip Length	Handle Length	Handle Material	Tip End	Quantity per Bag	
<b>Foam Swab</b>							
	813-10	6"	0.6"	5.5"	Wood	Single	10
	813-50	6"	0.6"	5.5"	Wood	Single	50
	813-250	6"	0.6"	5.5"	Wood	Single	250
	813-1000	6"	0.6"	5.5"	Wood	Single	1 000
<b>Rectangular Foam Swab</b>							
	814-10	5.5"	0.9"	4.5"	Polypropylene	Single	10
	814-50	5.5"	0.9"	4.5"	Polypropylene	Single	50
	814-250	5.5"	0.9"	4.5"	Polypropylene	Single	250
	814-1000	5.5"	0.9"	4.5"	Polypropylene	Single	1 000
<b>Tapered Cotton Swab</b>							
	8112A-100	5.875"	0.5"	5.812"	Wood	Single	100
<b>Cotton Tipped Application Swab</b>							
	8113-25	3.2"	0.4"	2.5"	Polypropylene	Double	25
	8113-25000	3.2"	0.4"	2.5"	Polypropylene	Double	25 000

Note: All lengths are an approximation.

## Technical Support

Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at [www.mgchemicals.com](http://www.mgchemicals.com).

Email: [support@mgchemicals.com](mailto:support@mgchemicals.com)

Phone: +(1) 800-340-0772 (Canada, Mexico & USA)

+ (1) 905-331-1396 (International)

Fax: +(1) 905-331-2862 or +(1) 800-340-0773

Mailing address: **Manufacturing & Support**  
1210 Corporate Drive  
Burlington, Ontario, Canada  
L7L 5R6

**Head Office**  
9347-193rd Street  
Surrey, British Columbia, Canada  
V4N 4E7

## Disclaimer

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. *M.G. Chemicals Ltd.* does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.