



VT-533 3W LED EMERGENCY LIGHT 6400K



FEATURES

- Fitted with high efficiency SMD LED Chips
- High-performance Ni-Cd batteries made for Longevity & low maintenance.
- LEDs mounted on print circuit board - Viewing distance of 22 meters from one side
- Thermoplastic PC housing, Rectangular type plastic with different signs.
- Reliable Emergency backup of 3 hours.
- Maintained and Non Maintained operation
- 4 ways different legends available
- Wall/ceiling mounted
- Green light indicator
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	6400K
Model:	VT-533
Watts:	3
Lumens:	140
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	White
Body Type:	PC Cover
Dimension:	346x107x60mm
Operation Temperature:	-20°C to +45°C
Battery Charging Current:	70-150mA
Battery Discharge Current:	100-450mA
Working Time:	3 Hours
No. Of Led:	16
PF:	>0.45
LED Chip Type:	SMD
Beam Angle:	120°
Emergency Operation Time:	3 Hours
Battery Type:	Ni-Cd 3.6V, 1200mAh
CRI:	>80
IP Rating:	IP65
Energy Saving:	80 Energy
Charging Time:	24 hours

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

ROHS Certificate: [Check the certificate](#)

IP65
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	8437
Model:	VT-533
EAN:	3800157641296
Commodity Code:	9405104090

PACKAGING

Gross Weight (Kgs):	0.76
Unit CBM:	0.003458
Dimension:	346x107x60mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	420
Length (Box) mm:	120
Width (Box) mm:	65
Height (Box) mm:	360

