

6 ft Black USB 2.0 Extension Cable A to A - M/F

Product ID: USBEXTAA6BK



The USBEXTAA6BK 6-foot USB Extension Cable (A-A) features 1 USB A male connector and 1 USB A female connector, extending the connection between USB 2.0 devices by up to 6 feet - an ideal solution for better placement of peripheral devices, or adding flexibility to existing USB ports.

This high quality USB extension cable is fully rated for use with USB 1.1 and USB 2.0 devices, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend your USB connection to connect a USB printer or any USB peripheral device to a PC or Mac at high-performance data transfer speed

Features

- Designed and constructed to USB 2.0 specifications
- Molded strain relief
- Supports data transfer rates up to 480 Mbps

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Wire Gauge	24/28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.6 in [1.5 cm]
Product Height	0.6 in [1.4 cm]
Weight of Product	0.8 oz [24.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]

Package Height	0.0 in [0.1 mm]
----------------	-----------------

Shipping (Package) Weight	1.1 oz [30.0 g]
------------------------------	-----------------

What's in the Box

Included in Package	1 - 6 ft Black USB 2.0 Extension Cable A to A - M/F
---------------------	---

****Product appearance and specifications are subject to change without notice.***