



XS1000 external solid state drive (SSD)

USB 3.2 Gen 2 external drive

Kingston's XS1000 external SSD is an incredibly convenient file backup solution. Its sleek, compact form factor is designed to fit seamlessly into your lifestyle, allowing you to carry it anywhere with ease. Don't let its size fool you – this tiny powerhouse boasts speeds of up to 1,050MB/s¹ and high capacities of up to 2TB², providing ample speed and space to store your valuable data. It connects with the included USB Type-C³ to Type-A cable to provide unrivalled convenience and impressive storage capabilities. The XS1000 is your reliable companion for hassle-free file backup, ensuring your important documents, cherished memories and media files are always readily accessible. Say goodbye to bulk and hello to streamlined storage efficiency with the XS1000 external SSD.

- Compact, pocket-sized form factor
- Speeds up to 1050MB/s¹ with USB 3.2 Gen 2
- Increased storage up to 2TB²

Key Features

- **Ultimate portability**

Compact and weighing just under 29g, this sleek, all-black SSD fits in your palm, allowing you to take your files on the go effortlessly.
- **Reliable file backup**

Take it all with you. Transfer and store your documents, large photos and videos without interruption.
- **Increased storage**

Expand your digital library with high capacities up to 2TB² to preserve life’s cherished moments.
- **USB 3.2 Gen 2 support**

Achieve read/write speeds up to 1,050MB/s¹ with backwards compatibility to USB 3.2 Gen 1 ensuring seamless connectivity with legacy devices.

Specifications

Interface	USB 3.2 Gen 2
Speed ¹	Up to 1,050MB/s read, 1,000MB/s write
NAND	3D
Capacities ²	1TB, 2TB
Dimensions	69.54 x 32.58 x 13.5mm
Weight	28.7g
Casing material	Metal + plastic
Includes	12" USB-C to USB-A cable
Operating temperature	0°C~40°C

Storage temperature	-20°C~85°C
Warranty/support ⁴	Limited 5-year warranty with free technical support
Compatible with ⁵	Windows [®] 11, 10, macOS (v.10.15.x +), Linux (v. 4.4.x +), Chrome OS [™] , Android [™] , iOS/iPadOS [®] (v.13+)

Part Numbers

XS1000

SXS1000/1000G
SXS1000/2000G

Product Image



1. Based on internal testing. Speed may vary due to host hardware, software and usage. USB 3.2 Gen 2 host device required for optimal speeds.
2. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's [Flash Memory Guide](#).
3. USB Type-C[®] and USB-C[®] are registered trademarks of USB Implementers Forum. USB Type-C to Type-C cable not included.
4. Limited warranty based on 5 years or "SSD Life Remaining" which can be found using the Kingston SSD Manager (Kingston.com/SSDManager). A new, unused product will show a wear indicator value of one hundred (100), whereas a product that has reached its endurance limit of program erase cycles will show a wear indicator value of one (1). See [Kingston.com/wa](#) for details.
5. Compatibility with Windows, macOS, Linux, Chrome OS, iOS/iPadOS and Android devices may vary and is largely dependent on the host software/hardware (please see your host manufacturer's support site for capabilities). For Android/iOS/iPadOS devices, an additional OTG cable (not supplied by Kingston) may be required.



THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2024 Kingston Technology Europe Co LLP and Kingston Digital Europe Co LLP, Kingston Court, Brooklands Close, Sunbury-on-Thames, Middlesex, TW16 7EP, England. Tel: +44 (0) 1932 738888 Fax: +44 (0) 1932 785469 All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-01192024