



Trust Nouna Kids Headphones - Pink

Comfortable, personalisable kids headphones with colourful design and volume limitation

Article number: 25277

Barcode: 8713439252774

GTIN: 08713439252774

Core content

Brand	Trust
Product type	Kids Headphones
Colour	Pink
Key features	- Adjustable headband and soft, comfortable ear pads make these headphones perfect for children up to 10 years old - Eco-friendly design; made with 85% recycled plastics - Kids-proof headphones with colourful design and active volume limitation (max 85dB) - Safe to use from ages 4 and up (compliant with European safety standard EN71 for children) - Stickers allow kids to personalise their headphones and bring even more fun to their listening - Foldable, lightweight design makes these ideal for use in the car or on-the-go - Convenient in-line control on the 3.5mm cable offers easy access to all important functions - Call grandparents or other relatives with ease via the handy in-line microphone
Package contents	- Kids headphones - Sticker sheet
System requirements	- 3.5mm audio connection

Marketing

Extended retailer text	Feel the fun Designed with an adjustable headband, soft and comfortable earpads, and a colourful and sustainable design; the Nouna Kids Headset brings so much joy to kids' listening experiences. What's more, it even comes with included stickers for personalisable fun!
-------------------------------	--

Happy ears

Let kids dance, jump and enjoy their favourite tunes without any earache. With active sound limitation (max 85 dB); this headset is perfect for kids aged 4-10.

Made for adventurers

For future astronauts, doctors, climbers and everything in between; the Nouna is ideal for kids on the go. With a lightweight foldable design, take on planes, trains and automobiles – the choice is yours!

Specifications

Plastic material	rABS
------------------	------

Sustainability method	PCR
-----------------------	-----

Total weight	112 g
--------------	-------

Weight of main unit	112 g
---------------------	-------

Height of main product (in mm)	172 mm
--------------------------------	--------

Width of main product (in mm)	65 mm
-------------------------------	-------

Depth of main product (in mm)	197 mm
-------------------------------	--------

Background noise reduction	No
----------------------------	----

Software	No
----------	----

Controls	next prev play controls volume control
----------	--

Controls on earcap	No
--------------------	----

Remote control	wired
----------------	-------

LED indicators	No
----------------	----

Connection type	wired
-----------------	-------

Connector type	3.5mm
Connector style	straight
Cable style	round
Bluetooth	No
Microphone	Yes
Driver size	40 mm
Driver units	2
Frequency response	20 - 20.000 Hz
True Wireless Stereo (TWS)	No
Sound reproduction	Stereo
Audio channels	2.0
Active Noise Cancelling	No
Ear-cap construction	closed-back
Ear-cap contact pressure	normal
Earcup type	on-ear
Foldable	Yes
Magnet type	Neodymium
Output channels	2
Sensitivity	92 dB

Swivel earcups	Yes
Volume limit	85 dB
Ear-cup material	leather
Adjustable headband	Yes
Rotating earcups	No
Designed for gaming	No
IP Code (International Protectio...	no
Waterproof	No
Compatible Device Types	laptop gaming console pc smartphone tablet
Compatible Software Platforms	Windows
Compatible Consoles	Nintendo Switch Nintendo Switch Lite
Suitable for	Children

Main image

	25277_pictures_product_visual_1.tif ImageWidth: 5.000 px ImageHeight: 5.000 px ImageResolution: 300 dpi
--	---

Additional Product Images



25277_pictures_product_visual_2.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25277_pictures_product_visual_4.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25277_pictures_product_visual_3.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25277_pictures_product_side_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25277_pictures_product_front_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi



25277_pictures_product_extra_1.tif

ImageWidth: 5.000 px

ImageHeight: 5.000 px

ImageResolution: 300 dpi

Package Images



25277_pictures_package_visual_1.tif

ImageWidth: 5.000 px

ImageHeight: 4.999 px

ImageResolution: 300 dpi



25277_pictures_package_front_1.tif

ImageWidth: 1.550 px

ImageHeight: 2.269 px

ImageResolution: 300 dpi
