




808050L

**Phillips/Pozidriv/Slotted LED Light
Ratcheting Screwdriver with
Ratcheting Grip**



PRODUCT DETAILS

- Ratcheting bit holder screwdriver for 1/4" bits , for high working speed
- Two-component handle with textured finish for maximum torque and minimum effort
- 48 teeth ratcheting screwdriver which permits smooth operation and minimum rotation arc to catch the next pawl tooth
- Smooth ratcheting stroke, three position ratchet mechanism: forward, reverse and neutral next pawl tooth
- Magnetic blade secures bit in screwdriver and makes bit changing easy. Stainless steel blade
- Knurled blade makes the grip firm, providing finger tip control for faster turning
- Interchangeable bit storage compartment with release button for quick access
- Slide tray that keeps 6 different bits handy and secure: PH 1, PH 2, PZ 1, PZ 2, slotted 4,5 and 5,5
- Long-lasting LED lights mounted in front casing provide illumination in dark conditions
- 3 batteries & 2 lights. AG-3 4.5V battery type. It meets ROHS requirements
- In cardboard box with hanging hole
- * 808050L-SP1: spare led panel + 3 batteries AG-3, 4.5V



PRODUCT ATTRIBUTES

Product							
808050L	1/4 in	10x35 mm	135 mm	41.6 mm	135 mm	250 mm	215 g

Follow the Fish!

