

Chain Saw LXT®

DUC357Z



Technical specifications

Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max Output Power	610 W
Chain Oil Tank	0,15 L
Max. Chain Speed (No Load)	7,7 m/s
Chain Speed at Max. Power	7,7 m/s
chain bar length	350 mm (14")
Chain Pitch	3/8 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	52
Sound Power Level (L _{WA})	97 dB(A)
Sound Pressure Level (L _{pA})	86 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating

EAN 0088381769730

Link to product - www.makitauk.com



Related products

Standard AC

165246-6

Guide bar, 14" / 35 cm, 3/8", 1,1 mm



419288-5

Chain Protection Cover 14" / 35 cm



713099-3

Saw Chain 14



Other

User manual

Parts drawing