

Impact Wrench LXT®

DTW300Z

18V • 1/2" • 330 Nm • 0 – 3 200 min⁻¹

Extra-compact and efficient brushless impact wrench with three power settings

Powerful and extra-compact, 144 mm-long, 1/2" drive impact wrench. Small size and light weight make this tool easy to use, while offering a max. fastening torque of 330 Nm. Four power settings. A handy LED light. Body version, batteries sold separately.



Technical specifications

Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	12,5 m/s ²
Vibration Uncertainty (K Factor), Impact Tightening of Fasteners of the Maximum Capacity of the Tool	1,5 m/s ²
Voltage LXT	✓
Nominal Battery Voltage	18 V
Max Output Power	420 W
No load speed	0 - 1000 / 1800 / 2600 / 3200 min ⁻¹
Max Fastening Torque Impact Drill	100 / 160 / 210 / 330 Nm
Nut-busting torque	580 Nm
Tightening Capacity Standard Bolt	M10 - M20
Tightening Capacity High Tensile Bolt	M10 - M16
Impacts per Minute (IPM)	0 - 1800 / 2600 / 3400 / 4000 min ⁻¹

User benefits

- Extremely compact thanks to a brushless motor
- Low power consumption thanks to brushless motor
- The narrow design of the handle ensures excellent handling
- Battery protection system automatically shuts off power when the battery level is low
- XPT (Extreme Protection Technology) is engineered for improved dust and water resistance for operation in harsh job site conditions

EAN 0088381898003

Link to product - www.makita.uk.com



Related products

Standard AC

346317-0
Belt Hook



Optional AC

B-69733
Impact Socket Set 7 pcs



D-41517
Impact socket set 1/2", 9 pcs



134874-8
Extension bar 1/2", 100 mm



134877-2
Universal Joint 84 mm



B-40141
Impact Socket 1/2" 17 X 38 mm



B-40185
Impact Socket 1/2" 21 X 38 mm



B-40216
Impact Socket 1/2" 24 X 38 mm



B-40222
Impact Socket 1/2" 27 X 42 mm



B-40238
Impact Socket 1/2" 30 X 44 mm



837670-0
MakPac (2) Inlay



346317-0
Belt Hook



346449-3
Belt Hook



E-12354
Impact deep socket set, 3 pcs



Other

User manual

Parts drawing