

USB FAST CHARGER GaN PD 8 PORT 240W



Model TGR-USB-240W-8P

- Supports charging of up to 8 devices at the same time
- Latest GaN technology for ultra efficient charging in a small size with less heat
- Features a wide range 100-240vac input for World use
- Standard 2 pin Fig 8 C7 input - Can be used Globally
- No AC cable included
- Power Delivery PD 3.0 for ultra fast charging of your devices
- Dimensions: 100 x 91 x 33mm



The Tiger 240W 8 port USB Fast Charger combines 7 USB C ports and 1 USB A port to provide a comprehensive charging device, engineered using latest GaN technology for wide compatibility in an ultra compact, pocket sized footprint. Ideal for home or office use and perfect for travelling due to its small size.



Outputs: 240W with 7 USB C ports + 1 USB type A (8 Ports total) GaN Desktop Charger Input: 100V-240V, 50/60Hz, 2.5A
USB-C1: (100W) PPS 3.3V-21V/5A, 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/5A
USB-C2: (30W) 5V/3A, 9V/3A, 12V/3A, 15V/2A, 20V/1.5A
USB-C3/C4/C5/C6: (45W) 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/2.2.5A
USB-C7/USB A: (20W) 5V/3A, 9V/2.22A, 12V/1.67A
C1+C2= 65W+30W
C1+C3+C5 or C1+C4+C6=100W+45W+45W
C1+C3+C5+C7=100W+45W+45W+20W
Total Output: 240W Max
CE, UKCA safety approved
Power Cord Type: No AC cable is included so please remember to also order the required mains lead for your Country of use. The unit takes an industry standard 2 pin Fig 8 type C7 type cable (C8 input socket) which are widely available



TIGER POWER PRODUCTS – QUALITY & RELIABILITY