

SYLPIPE HIGH OUTPUT
SYLPIPE L300 500LM 830 HIGH OUTPUT
0090051



Product features

- LED T5 replacement batten, high output range: more lumens per meter with efficiency up to 125 lum/watt, seamless linking (up to 10M), ideal for direct lighting such as under cabinet or in kitchens, 120 degree beam angle, includes switch, includes 0.30m stripped cable, white polycarbonate body, includes standard and tilting brackets



PRODUCT OVERVIEW

Product name	SYLPIPE L300 500LM 830 HIGH OUTPUT
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109
E-number FI	4279461
Warranty	3 years
Fixture luminous flux (lm)	500
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	120
Photobiological Risk Group	RG1
Total power consumption (W)	4
Electrical protection	Class II
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK03
Product EAN number	5410288900513

DATA TABLE

General data	
Product name	SYLPIPE L300 500LM 830 HIGH OUTPUT
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
General application	Residential & Consumer, Retail
ETIM Class	EC000109

SYLPIPE HIGH OUTPUT

SYLPIPE L300 500LM 830 HIGH OUTPUT

0090051

E-number FI	4279461
Warranty	3 years

Optical data

Fixture luminous flux (lm)	500
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	120
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	4
Primary Supply/Product voltage - min (V)	220
Primary Supply/Product voltage - max (V)	240
Lamp power factor	0.5
Electrical protection	Class II
Control gear required	No
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz
Connectable conductor cross section - Max (mm²)	0.75

Lifetime data

Lifespan L70 B50	54000
Lifespan L80 B10	54000

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK03
Nominal Product Length (mm)	300
Nominal Product Width (mm)	24
Nominal Product Height (mm)	35
Weight (kg)	0.058

Packaging

Product EAN number	5410288900513
Packaging single length / height (cm)	45.2
Packaging single width (cm)	3.2
Packaging single depth (cm)	4.2
DUN14 (outer)	15410288900510
Units per outer package	40
Packaging outer length / height (cm)	47.8



SYLPIPE HIGH OUTPUT
SYLPIPE L300 500LM 830 HIGH OUTPUT
0090051

Packaging outer width (cm)	23.5
Packaging outer depth (cm)	28.7