

<b>Product Name</b>	<b>iX1300</b>
Scanner Type	Dual Path: Automatic Document Feeder (ADF) / Return Path - double sided scan
Image Sensor	Colour Contact Image Sensor (Front & Back)
Light Source	3 Colour LED (Red/Green/Blue)
Optical Resolution	600 dpi
Scanning Speed (A4 Portrait)	30 pages per minute (200 dpi - 300 dpi)
Standard Paper Sizes	A4, A5, A6, B5, B6, Business Card, Post Card, Letter, Legal Folded A3, B4 and Double Letter via Return Path
Custom Paper Sizes	ADF / Return Path: Minimum: 50.8 mm x 50.8 mm (2" x 2") Maximum: 216 mm x 360 mm (8.5" x 14.17")
Paper Weight	ADF: 40 g/m <sup>2</sup> to 209 g/m <sup>2</sup> (11 lb to 56 lb) <i>varies according to paper size</i> Return Path: 20 to 413 g/m <sup>2</sup> (5.4 to 110 lb), Booklet of 2 mm or less
Card Scanning	Return Path only: Portrait/Landscape, thickness up to 1.4 mm (including emboss)
Feeder Capacity	ADF: 20 sheets of standard A4 (80 g/m <sup>2</sup> ) <i>varies according to paper thickness</i>
Multi-feed Detection	Length detection
ScanSnap Home Image Processing Functions	Automatic Colour Detection, Automatic Cropping, Automatic Deskew, Automatic Rotation, Blank Page Detection, Brightness (B&W Only), Deskew by Document Text, Document Title Extraction, Document Type Detection, Increase Text Contrast, JPEG Compression, Reduce Bleed-through, sRGB, Vertical Streaks Reduction
Output File-types	JPEG, PDF, Searchable PDF. Password PDF, PDF/A (Windows® only). Editable MS Word, Excel & PowerPoint with ABBYY FineReader for ScanSnap™
USB Interface	USB 3.2 Gen 1 / 2.0 / 1.1 (Type-B Connector)
Wi-Fi Interface	IEEE802.11 b/g/n Frequency band: 2.4 GHz
Wi-Fi Modes	Access Point Connect Mode – for connecting to a modem/router Direct Connect Mode – for connecting directly to a mobile device
Power Consumption	Operating: 17 W or less Sleep: 1.7 W or less
Operating Environment	Temperature: 5°C to 35°C (41°F to 95°F) Relative humidity: 20% to 80% (Non-condensing)
Device Dimensions (W x D x H) <i>when closed</i>	296 x 114 x 87 (mm) 11.7" x 4.5" x 3.3"
Device Weight	2.0 kg (4.4 lb)
Device Driver	ScanSnap specific driver Windows®: Does not support TWAIN / ISIS® macOS®: Does not support TWAIN
Environmental Compliance	ENERGY STAR® / RoHS
Standard Warranty	1 Year

<b>Bundled Software</b>	
<b>Windows®</b>	<b>macOS®</b>
ScanSnap Home <sup>1</sup>	
ScanSnap Manager	
ABBYY® FineReader for ScanSnap™ <sup>1</sup>	
<i>Please note: an internet connection is required to download the bundled software</i>	

<sup>1</sup> Includes one User License

<b>Optional Accessories</b>		<b>Part Number</b>
ScanSnap Type-6 Carry Case	Protects the scanner from dust and scratches	PA03805-0002

Document Carrier Sheet (5 pack)	Transparent sleeves for scanning A3, small or damaged documents	PA03360-0013
Photo Carrier Sheet (3 Pack)	Transparent sleeves for scanning photographs and postcards	PA03770-0015
Booklet Carrier Sheet	Transparent sleeve that provides enhanced protection when scanning booklets	PA03795-0018
Cleaning Wipes	Specialist ScanSnap cleaning wipes (24 pack)	CON-CLE-W24
Consumable Kit: 3805-090SK	Includes 1 x Pick Roller, 3 x Pad Unit and 24 x F1 Cleaning Wipes. Estimated life 90K scans.	CON-3805-090SK
3 Year Extended Warranty	Extends the 1 Year Standard Warranty to 3 Years	U3-EXTW-DKT

***Detailed specifications and minimum system requirements can be found at [Scansnapit.com/xxxx](https://scansnapit.com/xxxx)***

***©2021 PFU Limited. All rights reserved. ScanSnap, ScanSnap Home, ScanSnap Manager and their logos are trademarks or registered trademarks of PFU Limited in Japan. ©2021 Fujitsu Limited. All rights reserved. Fujitsu, the Fujitsu logo and Infinity symbol are registered trademarks or trademarks of Fujitsu Limited in Japan and/or other countries. ©2021 ABBYY Software Ltd. All rights reserved. ABBYY and FineReader are trademarks of ABBYY Software, Ltd. which may be registered in some jurisdictions. ©2021 Microsoft Corporation. All rights reserved. Windows®, Word®, Excel®, PowerPoint® and their logos are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. ©2021 OpenText Corporation. All rights reserved. ISIS™ and its logo are registered trademarks of OpenText Corporation in the United States and/or other countries. Other company names and product names are the registered trademarks or trademarks of their respective companies.***