

[Home](#) > [Products](#) > [M7571-05](#)

M7571-05

2.54mm (0.1") Pitch Open Top Jumper Socket, multi-usage, gold, Blue**3D CAD**[Download CAD/ECAD Model](#)

Traceparts account required

**2.54mm (0.1") Pitch PCB Connector - M20 Series**



[View Technical Details & Downloads](#)

In Stock

[Check Availability](#)

[Order Sample](#)

RELATED PRODUCTS

MATINGS

ALTERNATIVES



M20-9981045

2.54mm (0.1") Pitch DIL Vertical Throughboard Pin Header, 6.1mm mating pin height, gold



M20-8761042

2.54mm (0.1") Pitch DIL SMT Pin Header, selective gold + tin, 10+10 contacts

M

2.

H



1 of 2

FURTHER DETAILS

Jump To:

Technical Details

Product Characteristics

Materials

Dimensions

Downloads

Product Information

Technical Documentation

Environmental Compliance



**End Stackable:**

Yes

Mating Pin Size:

0.64mm square

Number of Rows:

1

Connector Orientation:

Vertical

Country of Origin:

GB

Side Stackable:

Yes

Number of Signal Contacts:

2

Operating Temperature:

-40°C to +85°C

RoHS Status:RoHS Compliant (2015/863/EU) with
no Exemption required**Current Rating:**

3A at 25°C

Polarised:

No

Cuttable:

No

Materials**Finish / Plating on Contact Surface:****Housing Material:**



Phosphor Bronze

SELECTED

Packaging Style:

Bulk/Loose

Housing Colour:

Blue

Dimensions

Contact Pitch:

2.54mm (0.1")

Weight:

0.116g

Dimensions:

5.00 x 2.30 x 6.30

Downloads

Product Information

Product Training Module - Overview Guide to the Harwin M20 (2.54mm pitch) and M22 (2mm pitch) ranges

Product Datasheet - INDESS range: M20 and M22 (BBI)