

Triple Monitor Desk Mount For Up To Three 27in Screens, VESA 75x75/100x100, Tool-Less Arm Adjustments, C-Clamp/Grommet Mount, Spring-Assisted Arms

Product ID: 3MP2AG-MONITOR-ARM



This monitor desk mount is designed to support up to three 27-inch displays, creating an ergonomic multi-monitor setup that provides an extensive viewing area for productivity. The mechanical spring-assisted arms allow multiple adjustment to suit different ergonomic needs.

The unique top-screw desk clamp simplifies installation by enabling users to tighten the clamp from manually from above using a hex key or a hand drill, eliminating the need to go under the desk. In addition, the desk clamp is designed with an interchangeable C-clamp and grommet mount to accommodate desks up to 2 inches (50mm) thick, providing flexibility for different desk configurations.

The central monitor mount enables height adjustments along the 22-inch (562mm) pole, allowing users to customize the screen placement for maximum productivity and comfort. The outboard arms enable independent toolless height adjustment of up to 10in (255mm) with effortless one-touch motion. For additional adjustments, reposition the outboard arms along the pole for different height ranges. The arms can extend up to 28.4in (722mm) from the pole.

The articulating arms allow toolless adjustments of +/-180 horizontal swivel and +/-90 screen rotation on the VESA plates for portrait or landscape orientations. The VESA mounting plates allow for +/-90 display tilt to provide an ideal viewing angle.

To maintain an organized workspace, the adjustable arms feature cable management channels along the underside to keep cables out of sight, reducing clutter and contributing to a tidy setup. A cable clip on the pole also helps maintain an organized workspace.

Certifications, Reports and Compatibility

Applications

Features

- **DESK MOUNT MONITOR ARM:** Triple monitor VESA mount (75x75/100x100mm) supports up to 15.4lb (7kg) 27-inch displays; Dual articulating and height adjustable steel arms w/central fixed monitor mount; C-clamp/grommet mounting
- **QUICK INSTALLATION:** Unique top-screw desk clamp for hassle-free installation without the need to go under the desk; Interchangeable C-clamp/grommet mount for desks up to 2" (50mm) thick; Includes tools for arm tension adjustment; Quick release VESA plates
- **RANGE OF MOTION:** Ergonomic three-monitor mount features articulating mechanical spring arms with toolless adjustments of +/-180 horizontal swivel, +/-90 tilt, and +/-90 screen rotation for portrait and landscape orientations
- **ONE-TOUCH ADJUSTMENT:** Mechanical spring-assisted arms w/height range of 8.8inches (275mm) & max arm extension of up to 28.4inches (722mm) from the pole; Designed for adjustable arm height along the pole
- **ORGANIZED WORKSPACE:** Enhance productivity & multi-tasking on high-performance workstations; Multi-monitor mount with cable management channels along the arms to keep cables out of sight; A pole-mounted cable clip helps maintain a tidy setup

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	3
Mounting Options	Wall-Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

Weight Capacity (Per Display)	15.4 lb [7 kg]
Maximum Display Size	27"
Fits Curved Display	No
Fits UltraWide Displays	Yes

Height Adjustment	Yes
Minimum Height	8.9 in [225 mm]
Maximum Height	22.1 in [562 mm]
Minimum Arm Extension	3.1 in [80 mm]
Maximum Arm Extension	28.4 in [722 mm]
Maximum Arm Span	47.6 in [1208 mm]
Display Tilt	+90 / - 90
Swivel / Pivot	+180 / -180
Display Rotation	+90 / - 90
Anti-theft	No

Physical Characteristics

Color	Black
Construction Material	Aluminum, Steel, and Plastic
Product Length	4.6 ft [1.4 m]
Product Width	6.9 in [17.6 cm]
Product Height	25.6 in [64.9 cm]
Weight of Product	2.2 lb [1.0 kg]

Packaging Information

Package Length	15.6 in [39.5 cm]
Package Width	21.9 in [55.5 cm]
Package Height	4.5 in [11.5 cm]
Shipping (Package) Weight	19.6 lb [8.9 kg]

What's in the Box

Included in Package	2 - Spring Arm
	4 - Swivel Arm

- 1 - Pole
- 3 - VESA Monitor Mount
- 1 - Cable Management Clip
- 1 - 3mm Hex Key with Flat Screwdriver
- 1 - 6mm Hex Key
- 12 - M4x12mm Screws
- 12 - M4x16mm Screws
- 12 - M5x12mm Screws
- 12 - M5x16mm Screws
- 12 - Flat Washers
- 12 - Spacers
- 1 - Desk Clamp
- 1 - Shoulder Pole Mount
- 1 - Center Pole Mount
- 1 - Center Monitor Mount
- 1 - Tool Holder
- 1 - Grommet Clamping Plate
- 1 - Grommet Clamping Screw
- 1 - User Manual

****Product appearance and specifications are subject to change without notice.***