



Pushing Performance  
Since 1945

# M17 Crimp Contact 0,6mm,male,0,25-0,5mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 063 0000
Specification	M17 Crimp Contact 0,6mm,male,0,25-0,5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/21170630000">https://b2b.harting.com/21170630000</a>

## Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

## Version

Gender	Male
Manufacturing process	Turned contacts

## Technical characteristics

Conductor cross-section	0.25 ... 0.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 24 ... AWG 20
Stripping length	5 mm
Limiting temperature	-40 ... +125 °C

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Packaging size	100
Net weight	0.19 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140568716
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors